

# PROLINE-PC 20-Degree Control Compartment, fits 800mm wide, Lt Gray, Steel

## CATALOG NUMBER

---

### PC20A8



Reversible design provides 20-degree angled surface for mounting operator controls. Smaller angle maximizes mounting space available. Screw cover on the flat side allows easy access inside compartment. Screw cover has foam-in-place gasketing. Compartment is gasketed around the open rear surface to extend the UL and CSA rating to the control compartment interior. Ground stud and mounting hardware included.

## FEATURES

---

Reversible design

Screw cover on the flat side has foam in place gasket

Ground stud and mounting hardware included.

## PRODUCT ATTRIBUTES

---

Article Number: 37049

Height: 6.89in

Width: 31.17in

Depth: 12.75in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 14ga

Weight: 28.5lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**