

# ProLine 100mm Solid Base Cable Entry Gland Plate, Black, Steel

## CATALOG NUMBER

---

### PCEGP



Fits all standard ProLine 100-mm Solid Base gland openings. Solid Base gland openings. Can be used in place of standard solid gland plates furnished with 100-mm Solid Base. Adjustable opening for cable entry is foam-lined to maintain a dust-tight seal.

## INDUSTRY STANDARDS

---

UL Listed; Type 1

This component is rated UL Type 1. Installing this component on an enclosure brings the enclosure rating to UL Type 1.

## FEATURES

---

Fits all standard ProLine 100-mm Solid Base gland openings

Foam-lined cable entry ensures a dust-tight seal

## PRODUCT ATTRIBUTES

---

Article Number: 22469

Material: Mild Steel

Weight: 1.4lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 14ga

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**