

Containment System Chimney, 30.00x21.01x16.69, Black, Steel

CATALOG NUMBER

PCM2



Containment System Chimney directs hot exhaust air into drop ceiling, duct work or other means back to the computer room cooling devices.

FEATURES

Two sizes to fit various ceiling heights

Infinite adjustment between minimum and maximum extension

Bulb gasket seals against flat surfaces and ceilings

S-connectors provided for duct work connection

Purchase Chimney Ceiling Panel separately

Tool-less Ceiling Panels are easy to install and remove for cleaning and provide above-the-cabinet access to cables, equipment and systems

Sealed containment, Chimney comes in two heights to fit a wide range of applications

PRODUCT ATTRIBUTES

Article Number: 20787

Height: 30in

Width: 21.01in

Depth: 16.69in

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 18ga

Ceiling Height: 114.36 – 144.36in

Min H: 36.13in

Max H: 66in

Weight: 98lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE