

PROLINE-SY Cover for Lower Front PC/SY, fits 600mm, Brushed, SS304

CATALOG NUMBER

PCS86SS



Solid steel construction. Steel cover is finished in RAL 7035 textured light-gray polyester powder paint (except stainless steel). Seamless foam-in-place gasket assures watertight and dust tight seal. Semi-flush cover screws attach cover to frame. A ground stud is provided.

FEATURES

Seamless foam-in-place gasket assures watertight and dust tight seal

Semi-flush cover screws attach cover to frame. A ground stud is provided

PRODUCT ATTRIBUTES

Article Number: 32109

Height: 30.2in

Width: 23.31in

Depth: 0.69in

Material: Stainless Steel 304

Finish: Brushed

Thickness: 14ga

Weight: 15lb

ADDITIONAL PRODUCT DETAILS

Covers with openings precut for various manufacturers' HMI devices are available in 600-mm sizes. See Covers with OI Cutouts.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE