

Door with Polycarbonate Windows for Upper and Lower Front, fits 600mm PC/SY, Aluminum

CATALOG NUMBER

PDW86



Window Doors include foam-in-place gaskets provided for door and window seals. Window is .25-in.-thick and available in clear safety glass or gray-tint polycarbonate. Doors are hinged on the left. Hidden hinges have retained hinge pins. Window door has a 2-point latch system and a Small Flush Bezel with tool-to-open insert. Other inserts and a Flush Swing Handle also are available.

FEATURES

Window door has a 2-point latch system and a Small Flush Bezel with tool-to-open insert

Seamless foam in place gasket

PRODUCT ATTRIBUTES

Article Number: 89380

Material: Aluminum

Window Size: 25.43 x 25.39in; 25.39 x 17.56in

Window Material: Polycarbonate

Weight: 18.58lb

Color: Light Gray

Color Code: RAL 7035

Finish: Powder Coated

Thickness: 11ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE