

ProLine Window Doors, fits 1400x800mm, Aluminum, Glass

CATALOG NUMBER

PDWG148



Window Doors can be used on the front or rear of ProLine frames to provide viewing of electronic equipment. ProLine Window Doors are designed around a mild steel profile. They have 140-degree hidden hinges and a flush bezel latch that operates a 3-point latching mechanism (doors for 700-mm frames have 2-point latching). Doors have either a smoke-gray tinted polycarbonate or a clear safety glass window; 180-degree hinges are available (order separately).

FEATURES

Install easily on front or rear of enclosure frame; can be hinged on left or right

Have two grounding brackets

Have a .25-in.-thick window that provides maximum protection and viewing area

Have foam-in-place urethane gaskets for door and window to provide optimum sealing

PRODUCT ATTRIBUTES

Article Number: 90810

Material: Mild Steel

Window Size: 47.94 x 25.42in

Window Door Type: Mild Steel; Safety Glass

Safety Glass: 52.72 x 31.22in

Weight: 43lb

Color: Light Gray

Color Code: RAL 7035

Finish: Powder Coated

Thickness: 14ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE