



We connect and protect

**ProLine 200-mm Plinth Base, fits
1600x800mm, Black, Steel**

Catalog Number

PPB2168



- Plinth Bases install under an enclosure to provide space for cables to enter from below. A Plinth Base consists of eight corner supports connected to four access panels. The corner supports are cast aluminum. The access panels attach to the corner supports with screws. Plinth Bases include all necessary mounting hardware. Order a gland plate system to provide Type 12 protection when using a plinth base.

Features

- Consists of eight corner supports connected to four access panels
- Order a gland plate system to provide Type 12 protection
- Includes all mounting hardware

PRODUCT ATTRIBUTES

- Article Number: 23549
- Material: Mild Steel
- Weight: 57lb
- Color: Jet Black
- Color Code: RAL 9005
- Finish: Powder Coated
- Thickness: 16ga

Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective

owners. nVent reserves the right to change specifications without notice.
This document is system-generated.

nVent.com/HOFFMAN |