

PROLINE-PC Modular Enclosure Type 12, 1800x600x800, Lt Gray, Steel

CATALOG NUMBER

PPC1868



ProLine-PC Modular Enclosures are ideal for applications that require housing standard PCs and keyboards. A modular system, these enclosures provide multiple configuration possibilities—simply add components to the frame to create a single enclosure, or gang multiple enclosures for larger or more complex applications.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File Number E61997

cUL Listed per CSA C22.2 No 94; Type 12; File Number E61997

NEMA/EEMAC Type 12

CSA File Number 42186: Type 12

VDE IP55

IEC 60529, IP55

FEATURES

Frame is enclosed with solid sides, a solid top and a 100-mm solid base.

Three doors, two in front and one in back, provide convenient access

Sealed keyboard compartment maintains enclosure integrity when the compartment door is opened

The 19-in. diagonal top window door, hinged on the left, offers viewing access for a variety of monitor sizes and has a small flush swing handle with keylock for system security

The vented frame shelf in the top compartment is constructed of 14 gauge steel and is painted with RAL 7035 textured light-gray polyester powder paint

The ProLine keyboard compartment includes a locking feature, an angled palm rest, a cable access port for wiring and integral mouse pad holders for both left-handed and right-handed people

The accessory front opening accommodates a number of optional components, such as keyboard shelves and control compartments

The bottom compartment includes a solid door hinged on the left that has a small flush swing handle with key lock; compartment can be used to install computer equipment, panel-mounted equipment or rack mounted control systems

PRODUCT ATTRIBUTES

Article Number: 98830

Height: 70.87in

Width: 23.62in

Depth: 31.5in

Material: Stainless Steel; Stainless Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Top Door Opening Height: 37.72in

Top Door Opening Width: 21.1in

Bottom Door Opening Height: 29.09in

Weight: 351lb

ADDITIONAL PRODUCT DETAILS

100-mm solid base is included in the A dimension.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE