

# Partial Subpanel, 800x600, fits 1400H (min.), White, Steel

## CATALOG NUMBER

**PPP86**



Partial Subpanels have flanges on four sides. Panels can be positioned vertically in 25-mm increments and also can be positioned at any depth in 25-mm increments using the optional grid straps. All necessary mounting hardware is included.

## FEATURES

12 gauge steel; conductive or white painted finish

All necessary mounting hardware is included

Partial Subpanels have flanges on four sides for added strength.

Panels can be positioned vertically in 25-mm increments, but also can be positioned at any depth in 25-mm increments using depth-mounted grid straps for securing (sold separately)

## PRODUCT ATTRIBUTES

Article Number: 99250

Material: Mild Steel

Weight: 24lb

Color: White

Finish: Powder Coated

Thickness: 12ga

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**