

# ProLine Pagoda Exhaust Vent, Fits Solid Tops, 115v

## CATALOG NUMBER

**PPT1**

Pagoda Exhaust Vents can be field-installed on any ProLine or ProLine G2 solid top to provide active enclosure cooling.



## FEATURES

Axial fan and finger guard mounted in housing

Drip-protected, raised cover is removable from the inside of the enclosure

115V or 230V versions with lead wires

115V power cord option

Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1

Includes gasket and mounting hardware

## PRODUCT ATTRIBUTES

Article Number: 20459

Material: Mild Steel

Voltage AC: 115V

Hertz: 50/60Hz

Weight: 8lb

Color: Light Gray

Color Code: RAL 7035

Finish: Powder Coated

Thickness: 14ga

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**