

ProLine Server Cabinet, 1200x600x900mm, Lt Gray, Steel

CATALOG NUMBER

PSC1269



The passively cooled ProLine Server Cabinet has a front viewing window and a wheeled base for application mobility and repositioning.

FEATURES

Front window door with key lock and vents offers visibility and ventilation

Open base with casters and levelers

Fully perforated rear door promotes airflow providing passive cooling to equipment

2000-mm tall cabinets have split rear perforated doors

Both front and rear doors provide security via lockable handles

Quick-release latches on side panels provide easy service access

Fully perforated top cover with two cable entry ports for easy access and service

Mounting channels provide infinite front-to-back adjustment of rack angles

PRODUCT ATTRIBUTES

Article Number: 46509

Height: 50.59in

Width: 23.94in

Depth: 35.4in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Rack Units: 24U

Additional Rack Angles: PRA1912THL1

Weight: 260lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE