

ProLine Sloped-Front HMI Enclosure Type 12, 500x600x600mm, Lt Gray, Steel

CATALOG NUMBER

PST566



A truly modular, build-your-own system, ProLine Sloped-Front HMI Enclosure foundation is extremely adaptable for nearly any application. Full-front opening for door/cover options has a 5-degree slope. Rear opening(s) for door and cover options. Optional ProLine Frame Shelf or ProLine Grid System is recommended to provide a stationary platform for supporting deep equipment. The open bottom is suitable for joining the top to a 700-mm-tall ProLine frame.

FEATURES

Enclosure is available in three heights

The bottom of the 600x600-mm sizes can be joined through a base with cutout to a pedestal or pendant arm system

A support bracket allows the 600x600-mm sizes to be suspended from an overhanging pendant arm system

PRODUCT ATTRIBUTES

Article Number: 36469

Height: 19.69in

Width: 23.62in

Depth: 23.62in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 14ga

Front Opening: 17.31 x 21.11in

Rear Opening: 17.13 x 21.11in

Internal Mounting: 12.8in

Weight: 46.72lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE