

ProLine Sloped-Front HMI with Accessory Opening, 700x600x600mm, Lt Gray, Steel

CATALOG NUMBER

PST7A66



A truly modular, build-your-own system, ProLine Sloped-Front HMI Enclosure with Accessory Opening foundation is extremely adaptable for nearly any application. Upper front opening for door/cover options has a 5-degree slope. Lower section is suitable for keyboard or other front options. Rear opening(s) for door and cover options. The internal mounting hole pattern accommodates most ProLine internal accessories. Optional ProLine Frame Shelf or ProLine Grid System provides a stationary platform for supporting deep equipment. The open bottom is suitable for joining the top to a 700-mm ProLine frame.

FEATURES

Enclosure is available in two heights

The bottom of the 600x600-mm sizes can be joined through a base with cutout to a pedestal or pendant arm system

A support bracket allows the 600x600-mm sizes to be suspended from an overhanging pendant arm system

PRODUCT ATTRIBUTES

Article Number: 36539

Height: 27.56in

Width: 23.62in

Depth: 23.62in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 14ga

Front Opening: 25.22 x 21.11in

Rear Opening: 31.91 x 21.11in

Internal Mounting: 27.56in

Weight: 70lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE