

ProLine Transportation Base, 167x600x800mm, Black, Steel

CATALOG NUMBER

PTB168



ProLine Transportation Bases provide safe transportation for ProLine frames, from a single bay up to a maximum of 3000 mm (118.11 in.) in a multiple-bay system. Transportation bases can be configured in a variety of combinations. Constructed from 10 gauge steel and finished with RAL 9005 textured black polyester powder paint. Unique design allows ROL-A-LIFT® lifting access from each end. A removable gland plate allows wire access between bases. ROL-A-LIFT is a trademark of Skarnes Inc.

FEATURES

Removable side cover plates allows wire access between bases

Can be used across bayed enclosures up to a maximum of 300mm (118.11in.) total width

Maintains NEMA 12 rating without requiring gland plate

Gasket and installation hardware included

Unique design allows forklift access from each end

Can be configured in a variety of combinations

PRODUCT ATTRIBUTES

Article Number: 14157

Material: Mild Steel

Finish: Powder Coated; Steel/Black

Weight: 85lb

Color: Jet Black

Color Code: RAL 9005

Thickness: 10ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE