

QLine D EMC Enclosure Type 4X, 120x80x55mm, Light Gray, Polycarbonate

CATALOG NUMBER

Q1286PCEMC

QLINEDEMCPair Product Photo

QLine D polycarbonate EMC enclosures have contoured bodies and flush cover screws for an attractive, contemporary appearance while also providing EMC protection in corrosive environments.

INDUSTRY STANDARDS

- UL 508A Listed; Type 4, 4X, 12, 13
- cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997
- Enclosure flammability evaluated per UL 508A
- NEMA/EEMAC Type 4, 4X, 12, 13
- IEC 60529, IP66

FEATURES

- Body is impact-resistant polycarbonate
- EMC conductive coating in base and cover
- Gasket of silver/silicone
- Mounting holes molded directly under cover screws
- Cross-point captivated cover screws are stainless steel
- Mounting tracks along body side walls and bosses on cover for PC card installation
- Cover screws protected by removable caps that are both aesthetic and provide tamper resistance
- Molded internal pads for mounting optional panels, rails and other components
- Screws provided for mounting optional panel

PRODUCT ATTRIBUTES

- Article Number: 45679
- Height: 4.72in
- Width: 3.15in
- Depth: 2.17in
- Material: Polycarbonate
- Finish: Smooth Matte
- Color: Light Gray

Color Code: RAL 7035

Thickness: 0.12in

Interior Finish: EMC Conductive Coating

Internal Dimensions: 4.47 x 2.89 x 1.93in

Mounting: 4.25 x 1.97in

Weight: 0.3lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE