

QLine I EMC Enclosure Type 4X, 200x200x123mm, Polycarbonate

CATALOG NUMBER

Q202013PCEMC



The largest-size enclosures in the QLine EMC series, the screw-cover QLine I protects larger controls from electromagnetic interference in corrosive environments.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997

Enclosure flammability evaluated per UL 508A

NEMA/EEMAC Type 4, 4X, 12, 13

IEC 60529, IP66

FEATURES

Body is impact-resistant polycarbonate

Polycarbonate material is easily punched, drilled, filed or sawed

EMC coating in base and cover

Gasket of silver/silicone

Mounting holes molded directly under cover screws

Molded internal pads for mounting optional panels, rails and other components

Molded internal rails for mounting adjustable depth panel kit

Screws provided for mounting optional panel

Easily removable covers attached to body with strong, durable polyamide cross-point cover screws

PRODUCT ATTRIBUTES

Article Number: 45739

Height: 7.87in

Width: 7.87in

Depth: 4.84in

Material: Polycarbonate

Finish: Smooth Gloss

Color: Light Gray

Color Code: RAL 7035

Thickness: 0.14in

Interior Finish: EMC Conductive Coating

Internal Dimensions: 7.40 x 7.40in

Mounting: 7.09 x 7.09in

Weight: 2.4lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE