

We connect and protect

QLine I EMC Enclosure Type 4X, 300x200x123mm, Polycarbonate

Catalog Number

Q302013PCEMC

QLineIEMCPair Product Photo

- The largest-size enclosures in the QLine EMC series, the screw-cover QLine I protects larger controls from electromagnetic interference in corrosive environments.

Industry Standards

- UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997
- cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997
- Enclosure flammability evaluated per UL 508A
- NEMA/EEMAC Type 4, 4X, 12, 13
- IEC 60529, IP66

Features

- Body is impact-resistant polycarbonate
- Polycarbonate material is easily punched, drilled, filed or sawed
- EMC coating in base and cover
- Gasket of silver/silicone
- Mounting holes molded directly under cover screws
- Molded internal pads for mounting optional panels, rails and other components
- Molded internal rails for mounting adjustable depth panel kit
- Screws provided for mounting optional panel
- Easily removable covers attached to body with strong, durable polyamide cross-point cover screws

PRODUCT ATTRIBUTES

- Article Number: 46519
- Height: 11.81in
- Width: 7.87in

- Depth: 4.84in
- Material: Polycarbonate
- Finish: Smooth Gloss
- Color: Light Gray
- Color Code: RAL 7035
- Thickness: 0.14in
- Interior Finish: EMC Conductive Coating
- Internal Dimensions: 11.34 x 7.40in
- Mounting: 11.02 x 7.09in
- Weight: 3.2lb

Additional Product Details

Purchase panels separately

Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/HOFFMAN |