

nVent-HOFFMAN-Logo-Horizon Photo

We connect and protect

ZonEx SA Series Junction Boxes, 30x23x18cm, Aluminum

Catalog Number

SA302318

ZONEX SA Series Junction Boxes; hazardous location; Flame Proof; Fire Proof Enclosure; SA09

- Zonex SA series junction boxes are suitable for increased safety or intrinsically safe enclosures applicable for Zone 1, 2, 21 or 22 with ATEX and IECEx certifications. They can be supplied with multipolar terminal blocks or modular terminal blocks. They can also be equipped with pilot lights, push buttons and measuring instruments. Body and cover can be drilled and threaded according to customers' specifications. In accordance with rules, nVent HOFFMAN must perform the drilling.

Industry Standards

- ATEX Directive 94/9/EC
- EN 60079-0
- EN 60079-1
- EN 60079-7
- EN 60079-11
- EN 60079-31

Features

- Low copper aluminum alloy and stainless steel bolts and screws for corrosion resistance
- Screw cover configuration for easy access
- High temperature-resistant silicone gasket provides IP66 rating
- Fixed mounting holes for easy installation
- Internal mounting panel included
- Body and cover can be drilled according to customers' specifications

PRODUCT ATTRIBUTES

- Article Number: 28996
- Height: 12.01in
- Width: 9.06in
- Depth: 7.48in
- Material: Aluminum
- Finish: Epoxy Coated
- Color: Light Gray
- Color Code: RAL 7035
- Thickness: 0.16in
- Weight: 10.36lb

Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO

- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/HOFFMAN |