

ZonEx SA Series Junction Boxes, 47x30x18cm, Aluminum

CATALOG NUMBER

SA473018



Zonex SA series junction boxes are suitable for increased safety or intrinsically safe enclosures applicable for Zone 1, 2, 21 or 22 with ATEX and IECEx certifications. They can be supplied with multipolar terminal blocks or modular terminal blocks. They can also be equipped with pilot lights, push buttons and measuring instruments. Body and cover can be drilled and threaded according to customers' specifications. In accordance with rules, nVent HOFFMAN must perform the drilling.

INDUSTRY STANDARDS

ATEX Directive 94/9/EC
EN 60079-0
EN 60079-1
EN 60079-7
EN 60079-11
EN 60079-31

FEATURES

Low copper aluminum alloy and stainless steel bolts and screws for corrosion resistance

Screw cover configuration for easy access

High temperature-resistant silicone gasket provides IP66 rating

Fixed mounting holes for easy installation

Internal mounting panel included

Body and cover can be drilled according to customers' specifications

PRODUCT ATTRIBUTES

Article Number: 29023

Height: 18.5in

Width: 12.01in

Depth: 7.68in

Material: Aluminum

Finish: Epoxy Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 0.16in

Weight: 16.97lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE