

Syspend Sanitary HMI Swivel Base Bracket, 4x7x7, Brushed, SS304

CATALOG NUMBER

SSBBSS



Syspend Sanitary HMI Swivel Base Bracket provides a means of attaching tube to the floor or a machine. Arm can be rotated or turned 330 degrees. Syspend-Lok attachment method prevents tubes from turning and pulling out of fittings and provides a water-tight connection.

CERTIFICATIONS



FEATURES

Type 304 polished stainless steel

Includes 4 set screws that provide means of leveling the entire suspension system

Surface mounting fasteners are not provided

Syspend-Lok Wrench Head for attaching base bracket to tubes is included

Strap wrench or spanner wrench that opens to 80 mm or greater can also be used

Not compatible with Syspend Sanitary HMI Base Bracket Cover

Assembled Syspend Sanitary HMI Arm System has a max weight load of 90 lb. (40.8 kg)

PRODUCT ATTRIBUTES

Article Number: 19348

Height: 3.52in

Width: 6.5in

Depth: 6.5in

Material: Stainless Steel 304

Finish: Polished

Thickness: 0.45in

Weight: 7.9lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE