

# Fan Shroud Kits Type 3R, fits 10-inch fan, Gray ANSI 61, Mild Steel

## CATALOG NUMBER

**T10S3R**



Fan Shroud Kit, Type 3R, protects enclosure openings from rain, sleet and snow. It comes with a gasket, ventilation screen, and is available in both painted mild steel and stainless steel.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3R; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E61997

Maintains UL/cUL Type 3R rating when properly installed on UL/cUL Type 3R enclosure.

NEMA/EEMAC Type 3R

IEC 60529, IP22

## FEATURES

Two fan shrouds per package

Perforated ventilation screen

Pressure-sensitive adhesive-backed gasket and mounting hardware

## PRODUCT ATTRIBUTES

Article Number: 13862

Height: 12in

Width: 12in

Depth: 4.71in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Dimensions: 12.00 x 12.00in

Weight: 10.2lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**