

FTTX Fiber Optic Cabinet Package Type 4X Dual, 30x30x44, Lt Gray, AL

CATALOG NUMBER

T303044FTTXDA



Pad-mounted FTTX welded aluminum enclosures provide longlasting protection and manage fiber optic cable for broadband delivery in outdoor applications. Provided with or without back-up batter compartment.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3, 3R, 4, 4X, 12

EC60529, IP66

Designed to meet Telcordia NEBS™ GR-487, GR-63 and IEC 48D

EIA 310-D with 19-in. spacing for rack equipment

Cabinet is RoHS compliant

NEBS™ is a trademark of Telcordia

FEATURES

Standard pitched roof promotes water runoff

Available with either single- or dual-access doors on front and rear for convenient access

Available with or without battery compartment

3-point latching mechanisms and padlocking handles on doors provide security

Seamless foam-in-place gasket seals doors against moisture and dust

Wind latch mechanisms on doors control door when open for equipment maintenance

Removable lifting lugs (2) for easy installation

Rack angles adjustable for 19- or 23-inch spacing without modifications

Use cage nuts to mount equipment

Cabinet top insulation helps prevent the formation of condensation and reduce solar gain inside cabinet. Cabinet side insulation is optional

Base of cabinet has a 5.00-inch (127-mm) high aluminum mounting plinth to allow for cable alignment

Three pyramidal boots provided at base of cabinet for sealing various sizes of cables

All fasteners are stainless steel to maintain professional appearance in severe outdoor climate conditions

Article Number: 29188
Height (H): 30in
Width (W): 30in
Depth (D): 44in
Material: Aluminum
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035
Thickness (T): 0.125in
Rack Units: 10U
Weight: 228.9lb

FT75 Fiber Optic Cabinet (Without Battery Compartment)

Technical drawings showing the front, side, and top views of the FT75 Fiber Optic Cabinet (Without Battery Compartment). Dimensions are provided in inches and millimeters.

Front View Dimensions:

- Overall Width: 19.00 (482.5)
- Overall Height: 14.00 (355.6)
- Mounting Hole Spacing: 1.50 (38.1)
- Mounting Hole Diameter: 0.375 (9.525)
- Internal Width: 16.50 (417.8)
- Internal Height: 11.50 (292.7)
- Internal Mounting Hole Spacing: 1.50 (38.1)
- Internal Mounting Hole Diameter: 0.375 (9.525)

Side View Dimensions:

- Overall Depth: 10.00 (254.0)
- Internal Depth: 8.50 (215.9)
- Mounting Hole Spacing: 1.50 (38.1)
- Mounting Hole Diameter: 0.375 (9.525)

Top View Dimensions:

- Overall Width: 19.00 (482.5)
- Overall Depth: 10.00 (254.0)
- Internal Width: 16.50 (417.8)
- Internal Depth: 8.50 (215.9)
- Mounting Hole Spacing: 1.50 (38.1)
- Mounting Hole Diameter: 0.375 (9.525)

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE