

# Terminal Box 3-Phase Type 3R, 23.00x14.00x4.50, Gray, Steel

## CATALOG NUMBER

**TB3R203240**



Terminal Box, Type 3R are wire-splice boxes for outdoor commercial or industrial applications that have a feeder tap to branch circuits. Boxes are available in three- or four-wire configurations in sizes up to 400 A.

## INDUSTRY STANDARDS

UL 1773 Listed; Type 3R; File No. E256098  
UL 50, 50E Listed; Type 3R; File No. E27525  
cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525  
NEMA/EEMAC Type 3R  
IEC 60529, IP32

## FEATURES

- Grounding provisions
- Hub opening at top with cover
- Provisions for padlocking or seal
- Distribution lugs installed (see table for sizes)
- Knockouts on bottom of enclosure
- Removable cover
- Drip-shield top and seam-free sides, front and back
- Terminal Boxes are finished with paint over plated surfaces

## PRODUCT ATTRIBUTES

- Article Number: 17002
- Height: 23in
- Width: 14in
- Depth: 4.5in
- Material: Mild Steel
- Finish: Galvanized; Powder Coated
- Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Current: 200A

Number of Phases: 3Ph

Wire Size: (6) #6 - 350 MCM

Voltage AC: 120V; 240V

Bar Quantity: 4

Weight: 18lb

## ADDITIONAL PRODUCT DETAILS

---

TB3R401 is UL and cUL for copper conductor only.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE