

Thermoelectric Condensate Manager TE12, .75x6.25x2.50, Brushed, SS304

CATALOG NUMBER

TEC100WCMSS4



Thermoelectric Condensate Manager drains condensation to bottom of enclosure via vent drain. Includes all required hardware and vent drain.

INDUSTRY STANDARDS

Maintains UL/cUL Type 3R, 12, 4 and 4X rating when properly installed

FEATURES

Drains condensation to bottom of enclosure via vent drain (vent drain included with package)

Utilizes existing mounting holes and fasteners of thermoelectric cooler that requires no additional mounting

Maintains the integrity of Type 4 or Type 4X enclosure

Items ending in SS4 are stainless steel

Items ending in NM are non-metallic

PRODUCT ATTRIBUTES

Article Number: 25641

Height: 0.75in

Width: 6.25in

Depth: 2.5in

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 16ga

Weight: 2.5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE