

Utility Junction Cabinet Pnl 2 Park Stand StyleB, 11.66x21.50, White, Galv Steel

CATALOG NUMBER

UJP2G



Utility Junction (UJ) Cabinet provides sectionalizing and tap-point functionality for underground distribution systems. Available in a wide variety of single- and three-phase models, these enclosures are rated 15 and 25 KV at 200 or 600 amperes and will accept two-, three- and four-way junctions from all manufacturers.

INDUSTRY STANDARDS

RUS Approved

ANSI C57.12.28 Pad-Mounted Equipment Enclosure Integrity

FEATURES

Recessed stainless steel penta-head bolt with padlock security system standard on all models

5/8-11 threaded lifting provisions

Wind stop standard on all models (two stops provided if B dimension is greater than or equal to 42-inch (1067mm))

Ground nut for each phase

Full range of modifications available on request

When ordering UJ cabinets, customer may specify multiple mounting panel options, including mild steel, galvanized and stainless steel (panels must be purchased separately)

ANSI C57.12.28 Pad-Mounted Equipment Enclosure Integrity RUS Approved

PRODUCT ATTRIBUTES

Article Number: 17946

Height (H): 11.66in

Width (W): 21.5in

Material: Mild Steel

Finish: Powder Coated

Color: White

Thickness (T): 12ga

Parking Stand Quantity: 2

Weight: 11.7lb


Design Version: B

ADDITIONAL PRODUCT DETAILS

UJ303018A, UJ306018A and UJ306723A aluminum models are .125-inch (3.3mm) thick.

Catalog weights and dimensions are careful estimates but not guaranteed.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE