

Ultrx Enclosure Solid Door Type 4X, 600x600x200mm, Lt Gray, Fiberglass

CATALOG NUMBER

UU606020



Providing outstanding protection against corrosion and the elements, the clean lines and molded, embossed design of Ultrx fiberglass enclosures make them the most stylish and aesthetically pleasing of their class.

INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E61997
cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13;
File No. E619977

Enclosure flammability evaluated per UL 508A

Window flammability evaluated per UL 508A

Mounting brackets required to meet UL/CSA external
mounting requirements.

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements

CERTIFICATIONS



FEATURES

Compression-molded fiberglass material has excellent temperature and chemical resistance qualities and exhibits outstanding physical properties, including high-impact resistance

Fiberglass is easily punched, drilled, filed or sawed

Seamless foam-in-place gasket assures water-tight and dust-tight seal

Enclosure may be rotated 180 degrees for left and right hinging

Molded-in drip shields are standard with each enclosure

Impact-resistant polycarbonate window is permanently bonded in place

Fiberglass mounting brackets and stainless steel attachment screws are provided with each enclosure

Unique hinge design allows for standard 180 degree door opening with a maximum opening of 270 degrees

Door hinges are replaceable

Type 316 stainless steel quarter-turn latch

Optional keylocking or padlocking handle available

Molded-in DIN bosses

Molded bosses on door provide additional mounting provisions

Integral mounting rails provide infinite panel adjustment front to back

Optional data pocket is high-impact thermoplastic

PRODUCT ATTRIBUTES

Article Number: 33690

Height: 24.61in

Width: 24.09in

Depth: 8.98in

Material: Fiberglass

Finish: Smooth Matte

Color: Light Gray

Color Code: RAL 7035

Thickness: 0.15in

Door Type: Solid

Internal Dimensions: 23.94 x 23.43 x 8.66in

Mounting: 22.01 x 22.52in

Weight: 32.4lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately

When installing enclosures in a right-hand hinge application that involves vibration, HOFFMAN recommends the use of padlocking or key-locking quarter-turn latch accessories for door securement (UUHPL, UUHKL).

For CALIFORNIA residents only - WARNING: This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm. Please note that by posting this Proposition 65 warning, we are notifying you that one or more of the Proposition 65 listed chemicals may be present in this product. With HOFFMAN's products, the exposure to these chemicals may be of no significant risk to you, but out of caution and to ensure your well-being, we have elected to place this warning on our site to make sure our customers are informed. You can find more information at <http://www.oehha.ca.gov/proposition-65/about-proposition-65>.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE