

# Vortex Cooler Type 4, 2500BTU 115V, Brushed, Aluminum

## CATALOG NUMBER

**VC2516004**



Powered by compressed air, Vortex Cooling Systems generate chilled air to cool small enclosures without refrigerants or moving parts. These systems are exceptionally reliable and low maintenance, even in the harshest and dirtiest environments.

## INDUSTRY STANDARDS

UL508 Listed; Type 4; File No. E187045 (Type 4 Models)

UL508 Listed; Type 4X; File No. E187045 (Type 4X Models)

UL508 Listed; Type 12; File No. E187045 (Type 12 Models)

NEMA Type 4 Models:

Maintains UL/cUL Type 4 when properly installed on a UL/cUL Type 4 enclosure.

NEMA Type 4X Models:

Maintains UL/cUL Type 4X when properly installed on a UL/cUL Type 4X enclosure.

NEMA Type 12 Models:

Maintains UL/cUL Type 12 when properly installed on a UL/cUL Type 12 enclosure.

## FEATURES

Five-micron airline filter, 115 V solenoid

Thermostat

Ducting kit

Cooling capacities to 2500 BTU/Hr. (733 W)

## PRODUCT ATTRIBUTES

Article Number: 46699

Height: 9.94in

Width: 2in

Depth: 2in

Nominal Voltage: 115V

Nominal Capacity Btu/h: 2500Btu/h

Nominal Capacity Watts: 733W

Voltage AC: 100V

Material: Aluminum

Finish: Brushed

Weight: 5.3lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**