

# VM Pushbutton Flat Opaque Screw Cover Type 4X, 6.72x3.17x3.61, Lt Gray, Polyester, PBS2

## CATALOG NUMBER

**VM733-PBS2**



The VM Series enclosure is designed for use as insulated electrical junction boxes, terminal wiring boxes, instrument housings, electrical control boxes and push-button housings in wet, dusty and corrosive environments.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E192121  
cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13;  
File No. E192121

Enclosure flammability per UL 508A

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements

## CERTIFICATIONS



## FEATURES

Enclosures are maintenance free and corrosion resistant

Bases and covers are made from Valox® 357U that can withstand continuous temperatures up to 280°F (138°C)

Cover screw holes in corners are outside of the gasketed area

Continuous gaskets made of polyurethane foam guarantee optimal integrity

All enclosures can be easily modified to customer specifications

## PRODUCT ATTRIBUTES

Article Number: VM733-PBS2

Height: 6.72in

Width: 3.17in

Depth: 3.61in

Material: Polyester

Finish: Smooth Gloss

Color: Light Gray

Color Code: RAL 7035

Weight: 0.36lb

## ADDITIONAL PRODUCT DETAILS

---

PBS: 30.5 mm NEMA sized push-button holes and four non-metallic corner screws

PBM: 22.5 mm IEC sized push-button holes and four non-metallic corner screws

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**