

WaterShed Wallmount Sloped Top 1/4-Turn Latch Type 4X, 10x8x4, Brushed, SS 304

CATALOG NUMBER

WS100804SS



Specifically designed for use in sanitary washdown production environments, particularly food and beverage manufacturing. HOFFMAN WaterShed Enclosures feature a sloped top, sloped door edges, bullet-style hinges and additional unique features that facilitate washdown runoff.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File Number E61997

Mounting brackets required to meet UL/cUL external mounting requirement.

NSF 169

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth

Smooth Type 304 stainless steel lift-off bullet-style hinges

Hinges are shielded by door

Hinged side of door has provisions to allow direct flushing of hinge area

20-degree sloped top facilitates runoff of water and cleaning solutions and prohibits the placement of objects on the top of the enclosure

97-degree door opening

Door edges are sloped 20-degrees at top and bottom edges to facilitate runoff

Slanted flange trough collar prohibits pooling of fluids along the top edge of the enclosure opening

Stainless steel quarter-turn latches furnished with flush slotted insert

Seamless foam-in-place gasket

Self-grounding latch system with double seal

Bonding provision on door; grounding stud on body

Enclosures with 'A' dimension of 16.00 in. (406mm) or greater utilize NEMA style panels; models with 'A' dimension less than 16.00 in. (406mm) utilize Junction Box style panels

Mounting holes in back of body for direct mounting optional stand-off kit or mounting bracket kit

Furnished hardware kit consists of panel mounting fasteners grounding hardware and sealing washers for wall-mounting hole

PRODUCT ATTRIBUTES

Article Number: 30137

Height: 10in

Width: 8in

Depth: 4in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Latch Quantity: 1

Weight: 10.06lb

ADDITIONAL PRODUCT DETAILS

WS080604SS, WS100804SS, WS121006SS and WS141208SS do not accept print pockets.

Purchase panels separately. Optional stainless steel, conductive or aluminum panels are available.

WS603616SS back is 10 gauge stainless steel.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE