

WaterShed Wallmount Disconnect Enclosure Type 4X, 60x37x16, Brushed, SS304

CATALOG NUMBER

WS60HS3716SS



Specifically designed for disconnect applications in sanitary washdown production environments, such as food and beverage manufacturing. nVent HOFFMAN WaterShed Disconnect Enclosures feature a sloped top, sloped door edges, bullet-style hinges and additional unique features that facilitate washdown runoff.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 4X, 12; File No. E61997

Mounting brackets required to meet UL/cUL external mounting requirement.

NSF 169

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66

Meets NEMA Type 3RX requirements

FEATURES

Specifically designed for type 4x food & beverage industry, indirect contact zone applications.

Seams continuously welded and ground smooth

Smooth Type 304 stainless steel lift-off bullet-style hinges

Hinges are shielded by door edges

Hinged side of door has provisions to allow direct flushing of hinge area

20-degree sloped top

97-degree door opening

Door edges are sloped 20 degrees at top and bottom

Slanted flange trough collar along the top edge of the enclosure opening

Stainless steel quarter-turn latches with flush slotted insert

Seamless foam-in-place gasket

Self-grounding latch system

Bonding provision on door; grounding stud on body

Panel studs fit optional NEMA size panels

Adjustable door interlock bracket fastened to door

PRODUCT ATTRIBUTES

Article Number: 13644

Height: 60in

Width: 37in

Depth: 16in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Latch Quantity: 5

Weight: 205lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

Optional Stainless steel, composite and aluminum panels available for most sizes.

NOTE: nVent HOFFMAN cannot guarantee compatibility of disconnect configurations with third-party latching.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE