

WaterShed Freestand 3-Pt Latch Type 4X, 74x75x24, Brushed, SS304

CATALOG NUMBER

WS747524SS



The HOFFMAN WaterShed stainless steel Freestand enclosure, with its unique design and Type 4X rating, is a perfect fit for mounting electrical or high-tech electronic equipment in a variety of indoor and outdoor settings. Its unique features are specifically designed for use in sanitary washdown production environments like food, beverage, or pharmaceutical processing. However, these same features also are useful in petrochemical plants, pulp and paper facilities and waste-water treatment plants.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File Number E61997
cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File Number E61997

NSF 169

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66

FEATURES

Specifically designed for type 4x food & beverage industry, indirect contact zone applications.

Seams continuously welded and ground smooth

Smooth Type 304 stainless steel lift-off bullet-style hinges

Hinges are shielded by cover edges

Hinged side of cover has provisions to allow direct flushing of hinge area

20-degree sloped top facilitates runoff of water and cleaning solutions and prohibits the placement of objects on the top of the enclosure

97-degree door opening

Door edges are sloped 20 degrees at top and bottom edges to facilitate runoff

Slanted flange trough collar prohibits pooling of fluids along the top edge of the enclosure opening

Three-point latching operated by PowerGlide Type 316L padlocking stainless steel handles

Seamless foam-in-place one-piece gasket provides oil-tight and dust-tight seal against contaminants

Bonding provision on doors; grounding studs on body

Accessory mounting channel provided in enclosure top

Panel studs fit optional NEMA style panels

Mounting holes in bottom of enclosure for direct mounting or for optional sanitary legs and stainless steel floor stands

Furnished hardware kit consists of panel mounting nuts, grounding hardware and hole seals for mounting hole

PRODUCT ATTRIBUTES

Article Number: 13103

Height: 74in

Width: 75in

Depth: 24in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 12ga

Weight: 760lb

ADDITIONAL PRODUCT DETAILS

A x B x C are nominal dimensions.

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE