



54BB23EDL Rotary Limit Switch 108:1 Type 4 Watertight

By Gleason Reel
Catalog # [54BB23EDL](#)

Rotary Limit Switch 108:1 Type 4 Watertight



Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

Application

Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load.

Specifications

Nema Rating 4

Current

Circuits Normally Closed	2
Circuits Normally Open	2
Minimum Shaft Turns To Trip	2
Contacts	
Maximum Shaft Turns To Trip	96
Contacts	

Dimensions

Reset Shaft Turns	1.5
Over Travel Shaft Turns	11

General

Series	54 Series
Product Category	Limit Switches
UPC	783246013101

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)