



# 54BB73ECL Rotary Limit Switch 72:1 Fine Adjustment Type 4

By Gleason Reel  
Catalog # [54BB73ECL](#)

Rotary Limit Switch 72:1 Fine Adjustment Type 4



## Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## Application

Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load.

## Specifications

Nema Rating 4

## Current

|                                      |     |
|--------------------------------------|-----|
| Circuits Normally Closed             | 2   |
| Circuits Normally Open               | 2   |
| Minimum Shaft Turns To Trip Contacts | 1.5 |
| Maximum Shaft Turns To Trip Contacts | 64  |

## Dimensions

|                         |     |
|-------------------------|-----|
| Reset Shaft Turns       | 1   |
| Over Travel Shaft Turns | 7.5 |

## General

|                  |                |
|------------------|----------------|
| Product Category | Limit Switches |
| Series           | 54 Series      |

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)