



54EB23ECL Rotary Limit Switch 72:1 Long Dwell Cam Type 4

By Gleason Reel
Catalog # [54EB23ECL](#)

Rotary Limit Switch 72:1 Long Dwell Cam Type 4



Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

Application

Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load.

Specifications

Nema Rating 4

Current

Circuits Normally Closed	2
Circuits Normally Open	2
Minimum Shaft Turns To Trip	2
Contacts	
Maximum Shaft Turns To Trip	60
Contacts	

Dimensions

Reset Shaft Turns	1.5
Over Travel Shaft Turns	10

General

Product Category	Limit Switches
Series	54 Series

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)