



# 55-4E-2DP-WB-111 Series 55 Limit Switch DPDT

By Gleason Reel  
Catalog # 55-4E-2DP-WB-111

Series 55 Limit Switch DPDT



## Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

## General

|                  |                |
|------------------|----------------|
| Product Category | Limit Switches |
| Series           | 55             |

## Dimensions

|                                      |      |
|--------------------------------------|------|
| Circuits Normally Closed             | 2    |
| Circuits Normally Open               | 2    |
| Maximum Shaft Turns To Trip Contacts | 36.5 |
| Minimum Shaft Turns To Trip Contacts | 1    |
| Over Travel Shaft Turns              | 6    |
| Reset Shaft Turns                    | 0.5  |

## Certifications and Compliance

|             |   |
|-------------|---|
| Nema Rating | 4 |
|-------------|---|

## Product Assets

[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)  
[Brochures - GLEASON\\_Series55\\_BROCHURE](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)  
[Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)  
[Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)  
[Technical Solutions - GRD-55-4E-2DP-WB-111-SPEC-EN](#)



A proud member of the Hubbell Family.