



55-4E-4DP-WB-333-LD Series 55 Limit Switch DPDT

By Gleason Reel
Catalog # 55-4E-4DP-WB-333-LD

Series 55 Limit Switch DPDT



Features

- Easy, precision timing adjustment using standard screwdriver and provided tool
- Industrial grade oil-impregnated bronze bearings
- Switch terminal screws for quick wiring
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

Product Category	Limit Switches
Series	55

Dimensions

Circuits Normally Closed	4
Circuits Normally Open	4
Maximum Shaft Turns To Trip Contacts	275
Minimum Shaft Turns To Trip Contacts	5
Over Travel Shaft Turns	58
Reset Shaft Turns	6

Certifications and Compliance

Nema Rating	4
-------------	---

Product Assets

[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
[Brochures - GLEASON_Series55_BROCHURE](#)
[Engineering Drawing - Series 55 Rotary Limit Switch DXF](#)
[Engineering Drawing - Series 55 Rotary Limit Switch DWG](#)
[Installation Manuals - Limit Switch-Series 55 Adjustment and Maintenance Instruction 630535](#)
[Technical Solutions - GRD-55-4E-4DP-WB-333-LD-SPEC-EN](#)



A proud member of the Hubbell Family.