



## 4 Outlet Receptacle, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black, Single Pack

By Bryant  
Catalog # [1254BLK](#)

4 Outlet Receptacle, Straight Blade Devices, Quad-PLEX, Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black, Single Pack

### Features

- Robust Construction: Commercial/industrial grade with durable straight blade design
- Enhanced Safety Features: Offers 2-pole 3-wire grounding, 15A, 125V capacity
- Sleek and Practical Design: Discreet black finish, easy installation, reliable performance.

### Application

Commercial/Industrial

### Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator Yes

Standards - RoHS Compliance CM

Status

Nema Rating 5-15R

### Conductor

Number Of Wires 3-Wire

Wire Size #14 AWG to #12 AWG

Number Of Poles 2-Pole

### Configuration

Number Of Outlets 4

### Current

Current Rating 15 A

Amperage Rating 15 A



Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Terminals
Wattage	1875
Voltage Rating	125 V

### Dimensions

Display Size	Standard Sized Product
Length	4.3 in
Width	4.30 in
Weight	0.4 lb.
Height	0.92 in
Dimensions	4.3 in x 4.30 in x 0.92 in

### General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Color	Black
Item Type	Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Four Outlet Receptacle
Material	Composite
UPC	781786336339

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)