BRYANT®

# Straight Blade Devices, Receptacles, Hospital Grade QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # 1254HSA

Straight Blade Devices, Receptacles, Hospital Grade QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Blue

## Features

- Hospital Grade QUADPLEX Receptacle
- Surge Suppression
- Isolated Ground
- 15A 125V
- 2-Pole 3-Wire Grounding

## Application

Quad-Plex

## Specifications

| | |
|---|---|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator | No |
| Nema Rating | 5-15R |

## Conductor

| | |
|---|---|
| Number Of Wires | 3-Wire |
| Number Of Poles | 2-Pole |

## Configuration

| | |
|---|---|
| Number Of Outlets | 4 |

## Current

| | |
|---|---|
| Frequency Rating | 60 Hz |
| Amperage Rating | 15 A |
| Voltage Rating Description | 125 V |
| Current Rating | 15 A |
| Voltage Rating | 125 V |
| Wattage | 1875 W |
| Connectivity | Terminals |
| Phase | Single Phase |
| Current / Amperage Rating | 15 A |

## Dimensions

| | |
|---|---|
| Length | 4.3 in |
| Display Size | Standard Sized Product |
| Weight | 0.5 lb. |
| Height | 0.92 in |
| Width | 4.30 in |
| Dimensions | 4.3 in x 4.30 in x 0.92 in |

## General

| | |
|---|---|
| Color | Blue |
| Outlet | Straight Blade |
| Series | Hospital Grade |
| OEM Brand Name | Hubbell Bryant |
| UPC | 781786190061 |
| Type | Four Outlet Receptacle |
| Material - Mounting Hardware | Screw Mounting |
| Item Type | Smooth Face |
| Material | Composite |

## Logistics

| | |
|---|---|
| Carton Quantity | 10 |

## Operational

| | |
|---|---|
| Response Time | 5 |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Indicator(s) Type | LED Visual Status Indicator |

## Product Assets

Catalog [English]
Catalog Page [English]
Catalog Page [English]
Catalog Page [English]



© 2026 Hubbell Incorporated. All rights reserved