



Straight Blade Devices, Receptacles,
QUADPLEX Receptacle, Surge
Suppression, Isolated Ground, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant
Catalog # 1254SIA

Straight Blade Devices, Receptacles, QUADPLEX Receptacle,
Surge Suppression, Isolated Ground, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Ivory

Features

- QUADPLEX Receptacle
- Surge Suppression
- Isolated Ground
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Quad-Plex

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Configuration

Number Of Outlets	4
-------------------	---

Current

Frequency Rating	60 Hz
Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875 W
Connectivity	Terminals
Phase	Single Phase
Current / Amperage Rating	15 A



Dimensions

Length	4.3 in
Display Size	Standard Sized Product
Weight	0.5 lb.
Height	0.92 in
Width	4.30 in
Dimensions	4.3 in x 4.30 in x 0.92 in

General

Color	Ivory
Outlet	Straight Blade
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786190030
Type	Four Outlet Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Smooth Face
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Response Time	5
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Indicator(s) Type	LED Visual Status Indicator

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)