



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 20403

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Thermoset molded housing provides maximum heat resistance

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating Description	20 Amp /30 Amp
Current Rating	20A/30 A



Amperage Rating	20A/30 A
Voltage Rating Description	250 VDC/600 VAC
Phase	Single Phase
Connectivity	Terminal Screws
Voltage Rating	250 VDC/600 VAC

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.94 in
Height	1.75 in
Dimensions	3.28 in x 1.94 in x 1.75 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Item Type	20A/30A Single Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786618473

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)