



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Receptacle, 30A 250V DC/600V AC, Non-NEMA, Screw Terminal, Cast Aluminum

By Bryant  
Catalog # 21420

Locking Devices, Bryant Power Interrupting, Industrial, Flanged Receptacle, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Angled housing reduces the profile of the device and makes mating and un-mating easier
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

|                          |                  |
|--------------------------|------------------|
| Environmental Conditions | IP44 Suitability |
| EU RoHS Indicator        | No               |

Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #18 AWG to #8 AWG |
| Number Of Poles | 3-Pole            |

Current

|                                     |                |
|-------------------------------------|----------------|
| Current/Amperage Rating Description | 20 Amp /30 Amp |
| Current Rating                      | 20A/30 A       |
| Amperage Rating                     | 20A/30 A       |



|                            |                 |
|----------------------------|-----------------|
| Voltage Rating Description | 250 VDC/600 VAC |
| Phase                      | Single Phase    |
| Connectivity               | Terminal Screws |
| Voltage Rating             | 250 VDC/600 VAC |

Dimensions

|              |                             |
|--------------|-----------------------------|
| Display Size | Standard Sized Product      |
| Length       | 3.28 in                     |
| Width        | 1.94 in                     |
| Height       | 1.75 in                     |
| Dimensions   | 3.28 in x 1.94 in x 1.75 in |

General

|                              |                                  |
|------------------------------|----------------------------------|
| OEM Brand Name               | Hubbell Bryant                   |
| Style                        | Grounding                        |
| Color                        | Metallic                         |
| Item Type                    | 20A/30A Angled Single Receptacle |
| Material - Mounting Hardware | Screw Mounting                   |
| Type                         | Flanged Receptacle               |
| Material                     | Composite                        |
| UPC                          | 781786618633                     |

Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)