



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # 23005

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	20 Amp/10 Amp
Description	
Current Rating	20 A
Amperage Rating	20 A



Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC
Phase	Multi Phase
Connectivity	Screw Terminals
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC

Dimensions

Display Size	Standard Sized
Length	1.62 in
Width	1.62 in
Height	3.56 in
Dimensions	1.62 in x 1.62 in x 3.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Color	Black, White
Item Type	10A/20A Male Nylon Non-Grounding Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786618879

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)