



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # 23005G

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White



Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator Yes

Conductor

Number Of Wires 3-Wire
Wire Size #14 AWG to #10 AWG
Number Of Poles 2-Pole

Configuration

Cord Type All Listed Portables

Current

Current/Amperage Rating 20 Amp/10 Amp
Description
Current Rating 20A/10 A

Amperage Rating 20A/10 A
Voltage Rating Description 125 VAC/125 VDC/250 VDC/480 VDC
Phase Single Phase
Connectivity Screw Terminals
Voltage Rating 125 VAC/125 VDC/250 VDC/480 VDC

Dimensions

Display Size Standard Sized
Length 1.72 in
Width 1.72 in
Height 3.22 in
Dimensions 1.72 in x 1.72 in x 3.22 in

General

OEM Brand Name Hubbell Bryant
Style Grounding
Color Black, White
Item Type 10A/20A Male Nylon Plug
Material - Mounting Hardware Cord Mounted
Type Plugs
Material Composite
UPC 781786618886

Logistics

Carton Quantity 20

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)