



## Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, Non-NEMA, Screw Terminal, FS/FD Mounting

By Bryant  
Catalog # 25250

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black, FS/FD Mounting



### Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

### Application

Industrial Grade

### Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means  
EU RoHS Indicator No

### Conductor

Number Of Wires 5-Wire  
Wire Size #14 AWG to #10 AWG  
Number Of Poles 4-Pole

### Current

Current/Amperage Rating Description 20 Amp /30 Amp  
Current Rating 20A/30 A  
Amperage Rating 20A/30 A

Voltage Rating Description 250 VDC/600 VAC  
Phase Multi Phase  
Connectivity Terminal Screws  
Voltage Rating 250 VDC/600 VAC

### Dimensions

Display Size Standard Sized Product  
Length 4.56 in  
Width 2.84 in  
Height 1.69 in  
Dimensions 4.56 in x 2.84 in x 1.69 in

### General

OEM Brand Name Hubbell Bryant  
Style Grounding  
Item Type 20A/30A Flush Single Receptacle  
Material - Mounting Hardware Screw Mounting Receptacle  
Material Composite  
UPC 781786683402

### Logistics

Carton Quantity 8

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)