



# Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 50A 250V DC/600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 25403



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 600V AC/ 20A 250V DC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Metal housing for F.S. and F.D. boxes, Blue finish

## Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic housing provides protection from damage in harsh environments

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	25403
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Style	Grounding
Type	Receptacle
UPC	781786683808

## Dimensions

Dimensions	4.56 in x 2.84 in x 1.69 in
Display Size	Standard Sized Product
Height	1.69 in
Length	4.56 in
Width	2.84 in

## Electrical Ratings

Amperage Rating	20A/30 A
Connectivity	Terminal Screws
Current Rating	20A/30 A
Phase	Single Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 25403 Specification Sheet French](#)
- [Specifications - 25403 Specification Sheet English](#)