



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 250V DC/600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal and White

By Bryant
Catalog # 25415



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 250V DC/600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	5-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	4-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating Description	20 Amp /30 Amp
-------------------------------------	----------------

Current Rating	20A/30 A
Amperage Rating	20A/30 A
Voltage Rating Description	250 VDC/600 VAC
Phase	Multi Phase
Connectivity	Screw Terminals
Voltage Rating	250 VDC/600 VAC

Dimensions

Display Size	Standard Sized
Length	2.50 in
Width	2.50 in
Height	6.56 in
Dimensions	2.50 in x 2.50 in x 6.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Black
Item Type	20A/30A Male Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786684003

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)