



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum

By Bryant
Catalog # 26410

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel screws provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Only
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	60 Amp
Description	
Current Rating	60 A
Amperage Rating	60 A



Voltage Rating Description	600V AC
Phase	Multi Phase
Connectivity	Terminal Screws
Voltage Rating	600 VAC

Dimensions

Display Size	Standard Sized Product
Length	4.62 in
Width	3.50 in
Height	3.57 in
Dimensions	4.62 in x 3.50 in x 3.57 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Item Type	60A Single Receptacle
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Composite
UPC	781786584105

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)