



Locking Devices, Bryant Power Interrupting, Industrial, Female, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # 26418

Locking Devices, Bryant Power Interrupting, Industrial, Female, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel screws provide maximum termination strength and dependability
- Insulated, color coded metallic housing enhances safety and abuse resistance

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Conductor Range	#6 AWG to #4 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	60 Amp
Description	
Current Rating	60 A
Amperage Rating	60 A
Voltage Rating Description	600 VAC
Connectivity	Pressure Terminal Screws



Voltage Rating	600 VAC
Dimensions	
Display Size	Standard Sized Product
Length	3.18 in
Width	3.18 in
Height	6.52 in
Dimensions	3.18 in x 3.18 in x 6.52 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Yellow
Item Type	60A Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786584181

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)