



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant
Catalog # 26419

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated, color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	60 Amp
Description	
Current Rating	60 A



Amperage Rating	60 A
Voltage Rating Description	600 VAC
Phase	Multi Phase
Connectivity	Screw Terminals
Voltage Rating	600 VAC

Dimensions

Display Size	Standard Sized
Length	3.03 in
Width	4.65 in
Height	4.65 in
Dimensions	3.03 in x 4.65 in x 4.65 in

General

OEM Brand Name	Hubbell Bryant
Style	Grounding
Color	Yellow
Item Type	60A Male Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786584198

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)