



# Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue

By Bryant  
Catalog # 26519



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue

### Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated, color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

### Application

Extra Heavy Duty Industrial

### Specifications

EU RoHS Indicator No

### Conductor

Number Of Wires 5-Wire  
Wire Size #14 AWG to #10 AWG  
Number Of Poles 4-Pole

### Configuration

Cord Type All Listed Portables

### Current

Current/Amperage Rating 60 Amp  
Description  
Amperage Rating 60 A  
Phase Multi Phase  
Connectivity Screw Terminals  
Voltage Rating 600 VAC

### Dimensions

Length 3.03 in  
Width 4.65 in  
Height 4.65 in  
Dimensions 3.03 in x 4.65 in x 4.65 in

### General

Style Grounding  
Color Blue  
Material - Mounting Hardware Cord Mounted  
Type Plugs  
Material Composite  
UPC 781786574199

### Logistics

Carton Quantity 5

### Product Assets

[Catalog \[English\]](#)